




Smartindale Martindale Abrasion And Pilling Tester

The Smartindale is used for abrasion and pilling tests on fabrics. It uses a digital algorithm to create a Lissajous curve to drive the friction. It runs accurately without calibration. You can switch the abrasion and pilling tests with a one-click touch on the screen button. No need to change the pins. After over 10 million cycles of ultra-high-intensity friction testing (equal to three years of nonstop operation) with rubber samples and double weights, the Lissajous curve is still accurate and perfect. The flip cover design is easy to see and use. A world-class third-party testing organization in France is using this instrument. Testers recognize it as easy to use.

Smartindale Martindale Abrasion And Pilling Tester



- **One-touch switching between pilling and abrasion testing, more efficient**

One-touch switching of test modes (abrasion, pilling, or straightness) on the control panel. So you do not need to remove the cover and change the pin position.

- **The Lissajous curve is calibration-free, while the test is more reliable.**

Smartindale runs by an exclusive and patented digital algorithm that drives dual servo motors and precision slide rails, replacing the traditional mechanical analog drive to generate a perfect Lissajous curve. After over 10 million cycles of ultra-high-intensity friction testing (equal to three years of nonstop operation) with rubber samples and double weights, the Lissajous curve is still accurate and perfect. So the test is more reliable.

- **Flip-up cover for easy observation and operation**

The upper cover can be easily flipped up and locked with one hand, making it easy for the operator to observe the test; it also greatly facilitates the installation of consumables and samples; and the slow-lowering device of cover ensures the safety of operator and the machine.

- **Easy to use**

A world-class third-party testing organization in France is using this instrument. Testers recognize it as easy to use.

- **Smart Abrasion and Pilling Test**

The instrument connects to the SmarTexLab APP via IoT on a smartphone or computer. It then connects to ERP/LIMS through an API. The instrument can also connect directly to ERP/LIMS. Test sample information, test process and results can be uploaded to the system and summarized with other tests to output reports. You can communicate with ChiuVention customer service personnel online to get support quickly; receive reminders of instrument calibration, maintenance, and replacement of consumables; and perform OTA remote upgrades on a regular basis.



Power

220/110V 50/60Hz



Weight

90kg



Dimension

510*850*300 mm(W*L*H)

Accessories

Fuse tube	2pcs
Foam wool	9 pcs Φ38 mm
Wool felt	18 pcs Φ90 mm, Φ140 mm
Wool abrasive	9 pcs Φ140 mm
Sampling plate	3 pcs Φ38 mm, Φ90 mm, Φ140 mm
Sampler	1 pc for pilling test
Sampler	1 pc for abrasion test
Press	1 pc Φ126mm, 2.5kg
Fixture1	9 sets for pilling test
Fixture 2	9 sets for abrasion test
Weight 1	9 sets 12Kpa
Weight 2	9 sets 9Kpa
Rubber ring	9pcs
Test pen	1pc
Connection shaft	9pcs for pilling test
Connection shaft	9pcs for abrasion test
Stainless steel ring	9pcs 260g

Optional Accessories

EMPA990 rating chart card	1 set	knitted + Woven
SM50 rating chart card	1 set	IWS + ASTM
SM25 abrasion resistant wool cloth	1 pack	1.6 X 5m/pack
Sm26 woven wool felt	1 box	24 pcs/box Φ140mm
Sm26 woven wool felt	1 box	24 pcs/box Φ90 mm
SM28 polyurethane ether foam	1box	250 X 200mm/pc, 25pcs/box
Ball Plate		Φ120mm

Standards

ISO 12945-2-2020 ISO12947-1-1998 ISO12947-2-2016
ISO12947-3-1998 ISO12947-4-1998
GB/T 21196.1-2007 GB/T 21196.2-2007
GB/T 21196.3-2007 GB/T 21196.4-2007
GB/T 4802.2-2008 BS EN 530-2010
ASTM D4970/4970M-22 ASTM D4966-22

Optional Standards

BS EN 388-2016+A1-2018 Protective gloves for mechanical hazards;
BS EN 16094-2012 Laminated wood flooring,
Test method for the determination of micro-scratches;
ISO 17076-2-2011; GB/T 39507-2020